

# Pressure Sensor with IO-Link

## FX8P002

Part Number



- Compact, laser-welded V4A stainless steel housing
- Individual parameters configuration via IO-Link 1.1
- Outstanding measuring accuracy: ±0.5%
- Quick sensor replacement thanks to data storage

weFlux<sup>2</sup> pressure sensors precisely measure the relative pressure of any desired media to an accuracy level of ±0.5%. Depending on application requirements, either two switching outputs or one switching output and one analog output can be selected for the purpose of reading out measured values. Furthermore, weFlux<sup>2</sup> pressure sensors offer new dimensions in individual parameters configurability. Sensor parameters, filter and output functions, as well as the unit of measure of the measured values (bar, PSI or Pascal), can be flexibly adjusted.



### Technical Data

#### Sensor-specific data

Measuring Range	0...100 bar
Measurement Type	relative
Maximum overload pressure	200 bar
Bursting pressure	400 bar
Medium	Liquids, gases
Pressure Response Time (t90)	< 10 ms
Measuring error (total)	< 1 %
Temperature Coefficient Zero-Point	<± 0,15% /10K
Temperature Coefficient Range	<± 0,2% /10K

#### Environmental conditions

Temperature of medium	-25...125 °C**
Ambient temperature	-25...80 °C
Atmospheric humidity	100 % r.H.
Storage temperature	-25...80 °C
EMC	DIN EN 61326-2-3
Shock resistance per DIN IEC 68-2-27	50 g / 11 ms
Vibration resistance per DIN IEC 60068-2-6	10 g (10...2000 Hz)

#### Electrical Data

Supply Voltage	12...32 V DC
Current Consumption (Ub = 24 V)	< 15 mA
Number of Switching Outputs	2
Switching Output/Switching Current	100 mA
Switching Output Voltage Drop	< 1,5 V
Analog Outputs	1
Analog Output	4...20 mA/0...10 V
Current Output Load Resistance	< 500 Ohm
Voltage output load resistance	> 1 kOhm
Interface	IO-Link V1.1
Short Circuit Protection	yes
Reverse Polarity Protection	yes
Protection Class	III

#### Mechanical Data


Setting Method	IO-Link
Sensor element	Stainless steel diaphragm
Housing Material	1.4404
Material in contact with media	1.4404; 1.4548; FKM
Degree of Protection	IP68/IP69K *
Connection	M12 x 1; 4-pin
Process Connection	G 1/2"
{Dichtungsmaterial}	FKM

#### Safety-relevant Data

MTTFd (EN ISO 13849-1)	1157,11 a
Analog Output	
IO-Link	
Connection Diagram No.	139
Suitable Connection Equipment No.	2
Suitable Mounting Technology No.	903


\* Not UL certified

\*\* Sensors suitable up to 125 °C media temperature. During installation, please ensure that the sensor housing is adequately cooled by the surroundings.



All dimensions in mm (1 mm = 0.03937 Inch)

27



## Legend

+	Supply Voltage +	PT	Platinum measuring resistor
-	Supply Voltage 0 V	nc	not connected
~	Supply Voltage (AC Voltage)	U	Test Input
A	Switching Output (NO)	Ü	Test Input inverted
Ä	Switching Output (NC)	W	Trigger Input
V	Contamination/Error Output (NO)	W-	Ground for the Trigger Input
Ä	Contamination/Error Output (NC)	O	Analog Output
E	Input (analog or digital)	O-	Ground for the Analog Output
T	Teach Input	BZ	Block Discharge
Z	Time Delay (activation)	Awv	Valve Output
S	Shielding	a	Valve Control Output +
RxD	Interface Receive Path	b	Valve Control Output 0 V
TxD	Interface Send Path	SY	Synchronization
RDY	Ready	SY-	Ground for the Synchronization
GND	Ground	E+	Receiver-Line
CL	Clock	E-	Emitter-Line
E/A	Output/Input programmable	±	Grounding
	IO-Link	SnR	Switching Distance Reduction
PoE	Power over Ethernet	Rx+/-	Ethernet Receive Path
IN	Safety Input	Tx+/-	Ethernet Send Path
OSD	Safety Output	Bus	Interfaces-Bus A(+)/B(-)
Signal	Signal Output	La	Emitted Light disengageable
BL-D	Ethernet Gigabit bidirect. data line (A-D)	Mag	Magnet activation
EN0RS422	Encoder 0-pulse 0-0 (TTL)	RES	Input confirmation
		EDM	Contactor Monitoring

EN0RS422 Encoder A/Ä (TTL)

EN0RS422 Encoder B/B (TTL)

ENA Encoder A

ENB Encoder B

AMIN Digital output MIN

AMAX Digital output MAX

AOK Digital output OK

SY IN Synchronization IN

SY OUT Synchronization OUT

OLT Brightness output

M Maintenance

rsv reserved

Wire Colors according to IEC 60757

BK Black

BN Brown

RD Red

OG Orange

YE Yellow

GN Green

BU Blue

VT Violet

GY Grey

WH White

PK Pink

GNYE Green/Yellow

