










# **Electrical connection**

**Dimensions** 

Emitter





Receiver

# **Model Number**

### SLC30-1350/151

with 2 separate fail-safe semiconductor outputs

## **Features**

- Sensing range up to 15 m
- Resolution 30 mm (hand protection)
- Self-monitoring (type 4 according to IEC/EN 61496-1)
- Master/Slave detection, Plug and Play
- Start/Restart disable
- Degree of protection IP67
- Integrated function display
- Pre-fault indication
- Optional with relay monitor (Option
- Connection via appliance socket M12 x b1
- Safety outputs OSSD in potential-separated semiconductor version
- Protective field height up to 1800 mm

# **Pinout**





Receiver

# **Accessories**

# **PG SLC-1350**

Protective glass panes for SLC series

laser alignment aid for safety light cutrtains series SLC

199755\_eng.xml Date of issue: 2017-12-11

Material Housing

Optical face

CE conformity

CCC approval

TÜV approval

**UL** approval

Approvals and certificates

extruded aluminum profile, RAL 1021 (yellow) coated


CCC approval / marking not required for products rated ≤36 V


Plastic pane Per 4350 g


cULus Listed

CF

ΤÜV







# **Notes**

#### Master slave mode

Master: SLC..-... (semiconductor)

or

SLC ..-../31 (relay)

Slave: SLC..-...-S

Using slaves makes it possible to lengthen protective fields or to form protective fields that lie in more than just one level. When you select slaves that can be connected, you should take into consideration that the maximum number of 96 light rays must not be exceeded.

There are slaves for transmitters and receivers. These may simply be connected to the master light curtain. As many as 2 slaves may be connected respectively to the transmitter and receiver unit.

#### Installation:

- 1 The end cap should be screwed off for the light curtain (without cable gland).
- 2 The plug-in jumper on the connectors of the printed circuit board, which is now visible, should be removed.
- 3 The slave is designed so that the cap located on the cable connector can be plugged directly onto the open end of the light curtain with the printed circuit board.
- 4 After you have screwed on the connection cap, the system is complete.

# System accessories

- Mounting set SLC
- Test rods SLC14/SLC30/SLC60
- Protective glass pieces for SLC (to protect the optically functional surface)
- · Lateral screwed connection SLC
- · Profile alignment aid
- Laser alignment aid SLC
- Mirror for SLC (for securing hazardous areas on multiple sides)
- Ground pillar UC SLP/SLC
- Housing for pillar Enclosure UC SLP/SLC
- Collision protector Damping UC SLP/SLC

